

## Izbor koruznih hibridov za leto 2017

HIBRID	ZNAČILNOSTI HIBRIDA						NAMEN UPORABE			
	ZRELOSTNI RAZRED	TIP ZRNA	VIŠINA RASTLINE	MLADOSTNI RAZVOJ	SPROŠČANJE VLAŽNOSTI IZ ZRNJA	STAY GREEN EFEKT	SUŠENJE ZRNJA	SILIRANJE ZRNJA	SILIRANJE CELE RASTLINE	BIOPLIN
<b>LG 32.58</b>	260	PT	+++	++++	+++					
<b>LJ 275T</b>	275	PT	++	+++	+++					
<b>FEROXXY</b>	300	PT	++	+++	+++					
<b>MUSIXX</b>	300	PT	+++	++++	+++					
<b>DKC 3623</b>	300	Z	+++	++++	++++					
<b>LG 23.06</b>	300	Z	+++	+++	++++					
<b>LG 33.30</b>	300	Z	+++	+++	++++	●				
<b>LG 30.315</b>	310	Z	+++	++++	++++					
<b>DKC 4014</b>	320	Z	+++	+++	++++					
<b>CHAPALU</b>	330	Z	+++	+++	++++					
<b>LG 33.50</b>	340	TZ	++++	++++	++++	●				
<b>CONEXXION</b>	340	Z	+++	+++	++++					
<b>SHERLEY</b>	340	TZ	++++	+++	+++	●				
<b>DKC4522</b>	345	Z	+++	+++	++++					
<b>DKC 4590</b>	345	Z	+++	+++	++++					
<b>LG 30.369 (LIMANOVA)</b>	360	Z	+++	+++	++++					
<b>DKC 4608</b>	360	TZ	+++	++++	+++					
<b>DKC 4717</b>	370	Z	+++	+++	++++					
<b>FUTURIXX</b>	380	Z	++++	+++	+++					
<b>DKC 5031</b>	400	Z	+++	+++	+++					
<b>ACIMILL</b>	400	Z	++++	+++	++	●				
<b>DKC 5542</b>	480	Z	+++	+++	++					
<b>DKC 5830</b>	600	Z	++++	+++	+++	●				
<b>LG 30.220</b>	220	PT	++	++++	+++	●				
<b>LG 30.311</b>	320	PT	++++	++++	+++	●				
<b>LG 33.87</b>	380	TZ	++++	+++	+++	●				
<b>SHANNON</b>	400	Z	+++++	+++	++	●				
<b>LG 34.90</b>	430	Z	+++++	+++	++	●				
<b>AAPOTHEOZ</b>	450	Z	++++	+++	++	●				

HIBRID 2017

LEAN HIBRID 2017

OKOLJSKE ZAHTEVE	SETVENA NORMA V 1000 RASTLIN/HA			PRIMERENOST GLEDE NA TIP TAL			KAZALO	
	TOLERANCA NA VLAGO IN NIZKE TEMPERATURE V ZAČETKU RASTI	TOLERANCA NA POMANJKANJE VLAŽNOSTI	LAHKA TLA	TEŽKA TLA	SILAŽA	TEŽKA, VLAŽNA TLA		SREDNJA TLA
+++	+++	75-85	90-95	90-100				8
+++	+++	90-95	95-100					8
+++	+++	80-90	85-90	85-95				8
++++	++++	80-90	85-90	85-95				8
++++	++++	75	85-90	85-90				9
++	++++	80-90	80-95	90-100				10
+++	++++	80-85	85-90	85-95				10
+++	++++	75-80	80-85	85-90				9
+++	++++	75-80	80-85	85-90				9
+++	++++	75-80	80-85	85-90				10
+++	++++	70-80	75-85	85				10
++++	++++	75-80	85-90	80-90				11
++++	+++	70-80	80-85	85-95				11
+++	++++	70-75	80-85	80-90				11
+++	++++	70-75	80-85	80-90				11
+++	++++	75-80	80-85	80-85				12
++++	++++	75-85	80-90	85-90				12
+++	++++	65-75	80-85	80-85				12
+++	+++	75	80-85	85-90				13
+++	++++	70	75-80	80				13
+++	+++	70-75	75-80	80-85				13
+++	+++	65-75	80-85	80-85				13
+++	++++	65	70-75	70-80				13
++++	+++	80-85	85-90	85-100				17
++++	+++	75-80	80-85	80-90				9/17
+++	++++			65-80				18
+++	+++			75-85				18
+++	+++			70-80				19
+++	+++	70-75	75-80	75-80				19